

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	Fixed End Bearing Housing	Plate to support the two bearings at the fixed end	1
2	McMaster-Carr: 60355K505	Deep-groove bearing	3
3	McMaster-Carr: 97022A749	Lock-Nut #1/2-20 for preloading inner races	1
4	Floating End Bearing Housing	Plate to radially support the bearing at the floating end	1
5	McMaster-Carr: 1615T68 (modified)	Shaft	1
6	McMaster-Carr: 9714K340	Wave washer 1/2" for preloading inner races	1
7	McMaster-Carr: 91831A140	Round shim for separating outer races on fixed end	1
8	McMaster-Carr: 8982K37 (modified)	L-Bracket for Mounting to Optical Bench	2
9	McMaster-Carr: 92196A272	Socket Head Screw #10-32 for bearing housing to L-bracket mount attachment	8
11	McMaster-Carr: 90107A011	Flat Washer #10 for bearing housing to L-bracket mount attachment	8
12	McMaster-Carr: 91813A160	Hex Nut #10-32 for bearing housing to L-bracket mount attachment	8
13	McMaster-Carr: 92196A542	Socket Head Screw #1/4-20 for L-bracket mount to optical bench attachment	8

